



G Series Short Maintained Contact 3-Position Selector Switch Operator-2NO/2NC Contact Rating

By Killark
Catalog # [GO25-3G8G](#)

G Series - Aluminum Short Maintained Contact 3-Position Selector Switch Operator- 2NO/2NC Contact Rating

Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

Specifications

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
UL File Number	E12379
CSA File Number	LR11714



Buy America(n) Qualified

Contact Manufacturer

Current

Amperage Rating	10 A
Frequency Rating	50/60 Hz

General

Type	Selector Switch
Series	GO Series
UPC	783936097527
Color	Black

Operational

Action	Rotary
Actuator	3 Position Selector Switch

Product Assets

[Catalog \[English\]](#)