



GOB4-G233CN34CN

By Killark
Catalog # GOB4-G233CN34CN

G Series - Aluminum ATEX Certified Long 120V Illuminated Push Button (Push To Test Pilot Light) Operator - Green Lens With Blank Nameplate -1NO/1NC Contact Rating

Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

Application

G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures.

Specifications

Nema Rating	3, 4, 4X
UL File Number	E12379
ATEX File Number	03ATEX 1203 U
CSA File Number	LR11714
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer



Conductor

Number Of Poles	1
-----------------	---

Current

Frequency Rating	50/60 Hz
Amperage Rating	10 A
Voltage Rating	250 V
Contact Rating	• NEMA A600 - 7200 VA (make), 720 VA (break), 10A cont. @ 600V AC (thermal) • NEMA Q300 - 69 VA (make & break), 2.5A cont. @ 250V DC (thermal).

Dimensions

Gross Weight with Packaging	1
Depth	4 in

General

Color	Green
UPC	783936225661
Type	Indicator
Series	GO Series

Operational

Operating Cycles	10,000 operations
Actuator	Pilot Light and Momentary Pushbutton
Action	Momentary