



G Series -Long 120V Illuminated Push Button (Push To Test Pilot Light) Operator - Red Lens With Blank Nameplate - 1NO/1NC Contact Rating

By Killark  
Catalog # [GOB4-R233C N34-EL](#)

G Series - Aluminum Long 120V Illuminated Push Button (Push To Test Pilot Light) Operator - Red Lens With Blank Nameplate - 1NO/1NC Contact Rating

Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

Application

G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures.

Specifications

|                          |                                                                                                                                                                                                                                                     |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s)      | <ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups B, C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul> |
| EU RoHS Indicator        | Contact Manufacturer                                                                                                                                                                                                                                |
| Nema Rating              | 3, 4, 4X                                                                                                                                                                                                                                            |
| UL File Number           | E12379                                                                                                                                                                                                                                              |
| CSA File Number          | LR11714                                                                                                                                                                                                                                             |
| Buy America(n) Qualified | Contact Manufacturer                                                                                                                                                                                                                                |

Conductor

|                 |   |
|-----------------|---|
| Number Of Poles | 1 |
|-----------------|---|



Current

|                  |                                                                                                                                                                                                             |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Contact Rating   | <ul style="list-style-type: none"><li>• NEMA A600 - 7200 VA (make), 720 VA (break), 10A cont. @ 600V AC (thermal)</li><li>• NEMA Q300 - 69 VA (make &amp; break), 2.5A cont. @ 250V DC (thermal).</li></ul> |
| Amperage Rating  | 10 A                                                                                                                                                                                                        |
| Frequency Rating | 50/60 Hz                                                                                                                                                                                                    |
| Voltage Rating   | 250 V                                                                                                                                                                                                       |

Dimensions

|                             |      |
|-----------------------------|------|
| Gross Weight with Packaging | 0.37 |
| Depth                       | 4 in |

General

|        |              |
|--------|--------------|
| Type   | Indicator    |
| Series | GO Series    |
| UPC    | 783936041216 |
| Color  | Red          |

Operational

|                  |                                      |
|------------------|--------------------------------------|
| Operating Cycles | 10,000 operations                    |
| Action           | Momentary                            |
| Actuator         | Pilot Light and Momentary Pushbutton |

Product Assets

[Catalog \[English\]](#)