



# G Series Extended Spring Returned 3-Position Keyed Selector Switch Operator-Return to Center from Right- 2NO Contact Rating

By Killark  
Catalog # [GOL38L632D](#)

G Series - Aluminum Extended Spring Returned 3-Position Keyed Selector Switch Operator- Return to Center from Right- 2NO Contact Rating

## Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

## Application

G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures.

## Specifications

|                          |                                                                                                                                                                                                                                                     |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s)      | <ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups B, C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul> |
| EU RoHS Indicator        | Contact Manufacturer                                                                                                                                                                                                                                |
| Nema Rating              | 3, 4, 4X                                                                                                                                                                                                                                            |
| UL File Number           | E12379                                                                                                                                                                                                                                              |
| CSA File Number          | LR11714                                                                                                                                                                                                                                             |
| Buy America(n) Qualified | Contact Manufacturer                                                                                                                                                                                                                                |

## Conductor

|                 |   |
|-----------------|---|
| Number Of Poles | 1 |
|-----------------|---|

## Current

|                |                                                                                                                                                                                                      |
|----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Contact Rating | <ul style="list-style-type: none"><li>• 60A INRUSH @ 120 VAC</li><li>• 30A INRUSH @ 240 VAC</li><li>• 15A INRUSH @ 480 VAC</li><li>• 12A INRUSH @ 600 VAC</li><li>• 0.55A INRUSH @ 125 VDC</li></ul> |
|----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|



|                             |                             |
|-----------------------------|-----------------------------|
| Amperage Rating             | 10 A                        |
| Frequency Rating            | 50/60 Hz                    |
| <b>Dimensions</b>           |                             |
| Gross Weight with Packaging | 0.5                         |
| Width                       | 2.25 in                     |
| Height                      | 1.25 in                     |
| Length                      | 6.31 in                     |
| Dimensions                  | 6.31 in x 2.25 in x 1.25 in |
| <b>General</b>              |                             |
| Type                        | Selector Switch             |
| Series                      | GO Series                   |
| UPC                         | 783936226521                |
| Color                       | Black                       |
| <b>Operational</b>          |                             |
| Action                      | Rotary                      |
| Actuator                    | 3 Position Selector Switch  |

## Product Assets

[Catalog \[English\]](#)