



G Series Extended Spring Returned 3-Position Keyed Selector Switch Operator-Return to Center from Left- without Contacts

By Killark
Catalog # [GOL39R032D](#)

G Series - Aluminum Extended Spring Returned 3-Position Keyed Selector Switch Operator- Return to Center from Left- without Contacts

Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

Application

G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures.

Specifications

| | |
|--|--|
| <p>Hazardous Rating(s)</p> <p>EU RoHS Indicator</p> <p>Nema Rating</p> <p>UL File Number</p> | <ul style="list-style-type: none"> • Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2 <p>Contact Manufacturer</p> <p>3, 4, 4X</p> <p>E12379</p> |
|--|--|



| | |
|--------------------------|----------------------|
| CSA File Number | LR11714 |
| Buy America(n) Qualified | Contact Manufacturer |

Current

| | |
|------------------|----------|
| Amperage Rating | 10 A |
| Frequency Rating | 50/60 Hz |

Dimensions

| | |
|-----------------------------|-----------------------------|
| Gross Weight with Packaging | 0.5 |
| Width | 2.25 in |
| Height | 1.25 in |
| Length | 6.31 in |
| Dimensions | 6.31 in x 2.25 in x 1.25 in |

General

| | |
|--------|-----------------|
| Type | Selector Switch |
| Series | GO Series |
| UPC | 783936226590 |
| Color | Black |

Operational

| | |
|----------|----------------------------|
| Action | Rotary |
| Actuator | 3 Position Selector Switch |

Product Assets

[Catalog \[English\]](#)