



**Oh No!**  
IMAGE COMING SOON

GOL3BCN

By Killark  
Catalog # GOL3BCN

G Series - Aluminum ATEX Certified Extended 120V Pilot Light  
Operator -Blue Lens With Blank Nameplate

Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

Application

G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures.

Specifications

|                     |                                                                                                                                                                                                            |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Nema Rating         | 3, 4, 4X                                                                                                                                                                                                   |
| UL File Number      | E12379                                                                                                                                                                                                     |
| ATEX File Number    | 03ATEX 1203 U                                                                                                                                                                                              |
| CSA File Number     | LR11714                                                                                                                                                                                                    |
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups B, C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li></ul> |

EU RoHS Indicator

- Class III, Divisions 1 & 2  
Contact Manufacturer

Current

|                  |          |
|------------------|----------|
| Frequency Rating | 50/60 Hz |
| Amperage Rating  | 0.025 A  |
| Voltage Rating   | 250 V    |

Dimensions

|                             |                             |
|-----------------------------|-----------------------------|
| Height                      | 1.25 in                     |
| Width                       | 2.25 in                     |
| Length                      | 6.31 in                     |
| Gross Weight with Packaging | 0.5                         |
| Depth                       | 3-3/8 in                    |
| Dimensions                  | 6.31 in x 2.25 in x 1.25 in |

General

|        |              |
|--------|--------------|
| Color  | Blue         |
| UPC    | 783936225555 |
| Type   | Indicator    |
| Series | GO Series    |

Operational

|                  |             |
|------------------|-------------|
| Operating Cycles | 10,000 hrs  |
| Actuator         | Pilot Light |