



G Series -Extended 120V Pilot Light Operator - Frosted Lens With Blank Nameplate

By Killark
Catalog # [GOL3F](#)

G Series - Aluminum Extended 120V Pilot Light Operator - Frosted Lens With Blank Nameplate

Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

Application

G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3, 4, 4X
UL File Number	E12379
CSA File Number	LR11714



Buy America(n) Qualified Contact Manufacturer

Current

Amperage Rating	0.025 A
Frequency Rating	50/60 Hz
Voltage Rating	250 V

Dimensions

Gross Weight with Packaging	0.4
Depth	3-3/8 in
Width	2.75 in
Height	2 in
Length	6.75 in
Dimensions	6.75 in x 2.75 in x 2 in

General

Type	Indicator
Series	GO Series
UPC	783936226194
Color	White

Operational

Operating Cycles	10,000 hrs
Actuator	Pilot Light

Product Assets

[Catalog \[English\]](#)