



# G Series -ATEX Certified Extended 120V Pilot Light Operator -Frosted Lens With Blank Nameplate

By Killark  
Catalog # [GOL3FCN](#)

G Series - Aluminum ATEX Certified Extended 120V Pilot Light Operator -Frosted Lens With Blank Nameplate

## Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

## Application

G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures.

## Specifications

|                     |                                                                                                                                                                                                                                                     |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups B, C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul> |
| EU RoHS Indicator   | Contact Manufacturer                                                                                                                                                                                                                                |
| Nema Rating         | 3, 4, 4X                                                                                                                                                                                                                                            |
| UL File Number      | E12379                                                                                                                                                                                                                                              |
| CSA File Number     | LR11714                                                                                                                                                                                                                                             |



Buy America(n) Qualified      Contact Manufacturer

## Current

|                  |          |
|------------------|----------|
| Amperage Rating  | 0.025 A  |
| Frequency Rating | 50/60 Hz |
| Voltage Rating   | 250 V    |

## Dimensions

|                             |                             |
|-----------------------------|-----------------------------|
| Gross Weight with Packaging | 0.5                         |
| Depth                       | 3-3/8 in                    |
| Width                       | 2.25 in                     |
| Height                      | 1.25 in                     |
| Length                      | 6.31 in                     |
| Dimensions                  | 6.31 in x 2.25 in x 1.25 in |

## General

|        |              |
|--------|--------------|
| Type   | Indicator    |
| Series | GO Series    |
| UPC    | 783936225579 |
| Color  | White        |

## Operational

|                  |             |
|------------------|-------------|
| Operating Cycles | 10,000 hrs  |
| Actuator         | Pilot Light |

## Product Assets

[Catalog \[English\]](#)