



GOL3GCN

By Killark
Catalog # GOL3GCN

G Series - Aluminum ATEX Certified Extended 120V Pilot Light
Operator -Green Lens With Blank Nameplate



Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

Application

G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures.

Specifications

Nema Rating	3, 4, 4X
UL File Number	E12379
ATEX File Number	03ATEX 1203 U
CSA File Number	LR11714
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G

EU RoHS Indicator	• Class III, Divisions 1 & 2 Contact Manufacturer
-------------------	--

Current

Frequency Rating	50/60 Hz
Amperage Rating	0.025 A
Voltage Rating	250 V

Dimensions

Height	1.25 in
Width	2.25 in
Length	6.31 in
Gross Weight with Packaging	0.5
Depth	3-3/8 in
Dimensions	6.31 in x 2.25 in x 1.25 in

General

Color	Green
UPC	783936225586
Type	Indicator
Series	GO Series

Operational

Operating Cycles	10,000 hrs
Actuator	Pilot Light