



G Series Extended Maintained Contact 4-Position Selector Switch Operator - Blank Nameplate - Without Contacts

By Killark
Catalog # [GOL54H](#)

G Series - Aluminum Extended Maintained Contact 4-Position Selector Switch Operator - Blank Nameplate - Without Contacts

Features


- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

Application

G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3, 4, 4X
UL File Number	E12379



CSA File Number	LR11714
Buy America(n) Qualified	Contact Manufacturer

Current

Amperage Rating	10 A
Frequency Rating	50/60 Hz

Dimensions

Gross Weight with Packaging	0.5
Width	2.25 in
Height	1.25 in
Length	6.31 in
Dimensions	6.31 in x 2.25 in x 1.25 in

General

Type	Selector Switch
Series	GO Series
UPC	783936226439
Color	Black

Operational

Action	Rotary
Actuator	4 Position Selector Switch

Product Assets

[Catalog \[English\]](#)