



GUFS-1M - 180° 1/2" Iron, Swivel Elbow

By Killark
Catalog # [GUFS-1M](#)

180° 1/2" Iron, Swivel Elbow



Features

- Threaded for rigid conduit or IMC
- Smooth integral bushings to prevent damage to wires

Application

Allows conduit to be joined at angles ranging between 90° and 180°. A screwdriver is the only tool needed.

Specifications

EU RoHS Indicator	Contact Manufacturer
CSA File Number	LR11716
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
UL File Number	E10514
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Hub Size	1/2"
Length	5 in
Gross Weight with Packaging	1.95
Width	3 in
Height	3 in
Dimensions	5 in x 3 in x 3 in

General

Series	GUFS Series
Color	Glossy gray
Type	Swivel Elbow
Material	Iron
Finish Type	Zinc Plated
UPC	783936170398

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog \[English\]](#)