



GUM-O-EX - 4" Union, Aluminum, Male to Female, Quad Listed

By Killark
Catalog # [GUM-O-EX](#)

4" Union, Aluminum, Male to Female, Quad Listed



Features

- Threaded for rigid conduit or IMC
- Tapered threads (NPT)
- Strong and durable construction
- Certified QUAD LISTED

Application

Permits removal of equipment without turning or removal of conduit.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
IECEX File Number	IECEXITS09.0024U

EU RoHS Indicator
Buy America(n) Qualified
ATEX File Number

Contact Manufacturer
Contact Manufacturer
ITS09ATEX16417U

Dimensions

Gross Weight with Packaging	4
Hub Size	4"

General

Type	Male to Female Union
Series	GUM Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Natural
UPC	783936071855
Color	Silver

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)