



GUMFS-1M - 180° 1/2" Iron, Swivel Elbow

By Killark
Catalog # [GUMFS-1M](#)

180° 1/2" Iron, Swivel Elbow



Features

- Threaded for rigid conduit or IMC
- Smooth integral bushings to prevent damage to wires

Application

Allows conduit to be joined at angles ranging between 90° and 180°. A screwdriver is the only tool needed.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
UL File Number	E10514
CSA File Number	LR11716
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Gross Weight with Packaging	2.34
Hub Size	1/2"

General

Type	Swivel Elbow
Series	GUMFS Series
Material	Iron
Finish Type	Zinc Plated
UPC	783936170411
Color	Glossy gray

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog \[English\]](#)