



GUML-1-EX - 1/2" 90° Angle Union, Aluminum, Male to Female, Quad Listed

By Killark
Catalog # [GUML-1-EX](#)

1/2" 90° Angle Union, Aluminum, Male to Female, Quad Listed



Features

- Threaded for rigid conduit or IMC
- Tapered threads (NPT)
- Strong and durable construction
- Certified QUAD LISTED

Application

Permits removal of equipment without turning or removal of conduit.

Specifications

IECEX File Number	IECEXITS09.0024U
EU RoHS Indicator	Contact Manufacturer
ATEX File Number	ITS09ATEX16417U
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups A, B, C, D • Class I, Zones 1 & 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Hub Size	1/2"
Length	3 in
Gross Weight with Packaging	0.16
Width	2 in
Weight	0.16 lb.
Height	3 in
Dimensions	3 in x 2 in x 3 in

General

Series	GUM Series
Color	Silver
Type	90° Angle Union
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Natural
UPC	783936071862

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)