



GUML-2M - 3/4" 90° Angle Union, Iron, Male to Female

By Killark
Catalog # [GUML-2M](#)

3/4" 90° Angle Union, Iron, Male to Female



Features

- Threaded for rigid conduit or IMC
- Tapered threads (NPT)
- Strong and durable construction

Application

Permits removal of equipment without turning or removal of conduit.

Specifications

EU RoHS Indicator	Contact Manufacturer
CSA File Number	LR11716
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups A, B, C, D • Class I, Zones 1 & 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
UL File Number	E10514
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Hub Size	3/4"
Length	3 in
Gross Weight with Packaging	0.62
Width	2 in
Height	2 in
Dimensions	3 in x 2 in x 2 in

General

Series	GUM Series
Color	Glossy gray
Type	90° Angle Union
Material	Iron
Finish Type	Zinc Plated
UPC	783936012117

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog \[English\]](#)