



GZ Series 3 Position 1 Pole Momentary Left/Right Keyed Selector Switch - Extra Long Length 57mm, 3/4 NPSM

By Killark
Catalog # [GZL37C6](#)



3 Position 1 Pole Momentary Left/Right Keyed Selector Switch - Extra Long Length 57mm, 3/4 NPSM

Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread and M22x1.5 on request.
- Control operators can be grouped into a single assembly thus reducing installation time and cost.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2 • Zones 1 & 2 • Zones 21 & 22 • II 2 G Ex db IIC/IIB+H2Gb • II 2 D Ex tb IIIC Db
IECEX File Number	IECEX SIR 19.0054 U
EU RoHS Indicator	Contact Manufacturer
Nema Rating	Type 4X
UL File Number	E12379
Buy America(n) Qualified	Contact Manufacturer
ATEX File Number	SIRA 19ATEX 1171 U

Conductor

Number Of Poles	1
-----------------	---

Current

Amperage Rating	20 A
Frequency Rating	50/60 Hz

Dimensions

Width	1.8 in
Weight	0.45 lb.
Height	1.8 in
Length	5.2 in
Dimensions	5.2 in x 1.8 in x 1.8 in

General

Type	Selector Switch
Series	GZ Series
UPC	783936179094
Color	Black

Operational

Action	Rotary
--------	--------

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)