



HKH Series Control Station, Momentary Contact Single Push Button- Panel Mount- M20- - Stainless Steel 1b

By Killark
Catalog # [HKH1BSPAP11](#)

HKH Momentary Contact Single Push Button- Panel Mount- M20- - Stainless Steel 1b

Features

- Size 1 Control Stations available as 1a, 1b, & 1c as standard catalog number offerings for 1, 2 & 3 device openings and will accept 2-M20 entries in either end.
- Ammeters available in 1b & 1c.
- Size 2 Enclosures available as 2a & 2c for 2, 4 & 6 device entries in cover with ability to accept 2-M25 entries in either end.
- Operating Temperature of -50°C to +60°C.
- Explosion Protected contact blocks 690 VAC N.O. & N.C. capable of 20 Amps for Switching Duty and HP Ratings up to 1HP.
- LED Pilot Light modules for 12-250V AC/ DC for UL applications. 12-254V AC/DC for IEC applications.
- Contacts & Pilot lights can be mounted inside enclosure on Din Rail or in cover to the actuator.
- Accessories available for Lockout/Tag Out functions made in 316 stainless steel.

Application

Hazardous and corrosive environments due to the presence of flammable gases or vapors, combustible dusts or ignitable fiber or flyings, Installations at petroleum refineries, chemical and petrochemical plants and other processing or storage facilities where similar hazards exist, Use in conjunction with motor starters or contactors for remote control of motors

Specifications

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class II, Division 1, Groups E, F, G (Canada Only) • Class II, Division 2, Groups E, F, G • Class III, Divisions 1 & 2
---------------------	---



IECEX File Number	15.0054X
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3, 4, 4X, 12, 13
UL File Number	E53360
Buy America(n) Qualified	Contact Manufacturer
ATEX File Number	1405X

Current

Amperage Rating	20 A
Frequency Rating	50/60 Hz

Dimensions

Depth	4.25 in
Hub Size	M20
Weight	1.66 lb.

General

Series	HKH Series
Material	Stainless Steel, Type 316
UPC	783936130200
Color	Choice of Red, Green, Black
Mounting Type	Wall

Operational

Operating Temperature Range	-50°C to 60°C
Celsius	
Action	Momentary
Actuator	Pushbutton
Horsepower - Maximum	1

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)