



HKH Series 20A Factory Sealed Contact Block - NO Contact - Din Rail Mount

By Killark
Catalog # [HKH1NO20D](#)

HKH 20A Factory Sealed Contact Block - NO Contact - Din Rail Mount

Features


- Explosion Protected Din Rail contact block 690VAC N.O. & N.C. capable of 20 Amps for Switching Duty and HP Ratings up to 1HP.

Application

Contact block shall be installed in a Class I, Zone 1, AEx e II/Ex e IIC increased safety enclosure with a minimum IP54 rating or a Class I, Zone 1, AEx d IIC/Zone 21, Aex tb minimum IP64 rating, where the suitability is determined in the end application.

Specifications

Hazardous Rating(s)	- Class I, Division 2, Groups A, B, C, D - Class I, Zones 1 & 2
IECEx File Number	12.0033U
EU RoHS Indicator	Contact Manufacturer
UL File Number	E12379
Buy America(n) Qualified	Contact Manufacturer
ATEX File Number	1202251U



Current

Amperage Rating	20 A
Frequency Rating	50/60 Hz
Voltage Rating	24-690 AC/DC V

General

Series	HKH Series
UPC	783936092652

Logistics

Carton Quantity	20
-----------------	----

Operational

Operating Temperature Range Celcius	-40°C to 55°C
Action	Momentary
Horsepower - Maximum	1

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)