



K050 - 1/2" Straight Liquidtight Connector Non-Insulated

By Killark
Catalog # [K050](#)

1/2" Straight Liquidtight Connector Non-Insulated



Features

- Split nylon gland ring for easy installation and greater compression
- Digging locknut
- Sealing o-rings included
- Reusable

Specifications

EU RoHS Indicator	Contact Manufacturer
CSA File Number	LR70873
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(B) (Class I, Division 2) or 502.10(A)(B) (Class II, Divisions 1 & 2) and 505.15(C) (Class I Zone 2).
UL File Number	E22699
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Hub Size	1/2"
Weight	0.17 lb.

General

Series	K Series
Insulation Type	Non-insulated
Style	Straight
Color	Gray
Type	Straight Liquidtight Non-Insulated Connector
Material	Steel
UPC	783936997933

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog \[English\]](#)