



K1009 - 1" 90° Liquidtight Connector Non-Insulated

By Killark
Catalog # [K1009](#)

1" 90° Liquidtight Connector Non-Insulated



Features

- Split nylon gland ring for easy installation and greater compression
- Digging locknut
- Sealing o-rings included
- Reusable

Specifications

Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(B) (Class I, Division 2) or 502.10(A)(B) (Class II, Divisions 1 & 2) and 505.15(C) (Class I Zone 2).
EU RoHS Indicator	Contact Manufacturer
UL File Number	E22699
CSA File Number	LR70873
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Hub Size	1"
----------	----

General

Type	90 Degree Liquidtight Non-Insulated Connector
Series	K Series
Material	Steel
Insulation Type	Non-insulated
UPC	783936991351
Style	90 Degree
Color	Gray

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)