



K12541-MG - 1 1/4" 45° Liquidtight Connector w/Mesh Grip

By Killark
Catalog # [K12541-MG](#)

1 1/4" 45° Liquidtight Connector w/Mesh Grip



Features

- Split nylon gland ring for easy installation and greater compression
- Digging locknut
- Sealing o-rings included
- Reusable

Specifications

Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(B) (Class I, Division 2) or 502.10(A)(B) (Class II, Divisions 1 & 2) and 505.15(C) (Class I Zone 2).
EU RoHS Indicator	Contact Manufacturer
UL File Number	E22699
CSA File Number	LR70873
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Hub Size	1-1/4"
----------	--------

General

Type	45 Degree Liquidtight Insulated Connector W/Mesh Grip
Series	K Series
Mesh Grip	Yes
Material	Steel
Insulation Type	Nylon
UPC	783936383460
Style	45 Degree
Color	Gray

Logistics

Carton Quantity	2
-----------------	---

Product Assets

[Catalog \[English\]](#)