



K20041-G - 2" 45° Liquidtight Connector Insulated Grounding Lug

By Killark
Catalog # [K20041-G](#)

2" 45° Liquidtight Connector Insulated Grounding Lug



Features

- Lay-in grounding lug
- Plated steel for excellent durability
- Insulated throat fittings protect conductors from insulation damage

Specifications

Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(B) (Class I, Division 2) or 502.10(A)(B) (Class II, Divisions 1 & 2) and 505.15(C) (Class I Zone 2).
EU RoHS Indicator	Contact Manufacturer
UL File Number	E22699/E152165
CSA File Number	LR70873
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Hub Size	2"
----------	----

General

Type	45 Degree Liquidtight Grounded Insulated Connector
Series	K Series
Grounding Style	External Lug
Material	Iron, Malleable
Insulation Type	Nylon
UPC	783936383774
Style	45 Degree
Color	Gray

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog \[English\]](#)