



KFL2033 - KFL-X 20000 LUMEN 347-480 VAC 50/60 Hz 5000K CCT 70 CRI

By Killark
Catalog # [KFL2033](#)

KFL-X 20000 LUMEN 347-480 VAC 50/60 Hz 5000K CCT 70 CRI

Features

- Standard 6KV surge protection
- Optional supplementary surge protection available 20KA/10KV (120-277 VAC), 10KA/10KV (347-480 VAC)
- Crisp White Light for Excellent Color Rendering - Chromaticity 5000 K (CCT) approx. 70 CRI
- Energy Savings - High lumens per watt
- Long Life - 100,000+ maintenance free hours to 70% initial lumens
- Ambient suitability -50°C to 65°C
- World Voltage 120 - 277VAC 50/60Hz
- Instant On - Including after power interruption
- Solder-LESS LED Board Connections - Vibration Resistant

Specifications

EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Current

Frequency Rating	50/60 Hz
Wattage	180 W
Voltage Rating	347-480 VAC



Dimensions

Hub Size	3/4 NPT or M25
----------	----------------

General

Type	Floodlight
Series	KFL-X Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Optic Type	Glass Lens
UPC	783936186030
Light Source	LED

Operational

Color Temperature	5000 K
Operating Temperature	-50°C to +55 °C
Lumen Range	15,001-25,000 lm

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)