



KP Series 30 Amp Plug - D Type - 3P 4W Circuit - Grommet Range 0.375-0.625 Inch - 115/230VAC At 60Hz

By Killark
Catalog # [KP-304D23](#)

KP Series - Aluminum 30 Amp Plug - D Type - 3W 4P Circuit - Grommet Range 0.375-0.625 Inch - 115/230VAC At 60Hz

Features

- Suitable where a connection is required for portable or movable equipment such as tools, motors, hand lights, etc.
- Solder Terminations for sure connection
- Copper free aluminum housing
- Delayed action contacts ensure safe interconnect
- Wide range of grommet openings
- Extra long grounding pin makes contact first and breaks contact last

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB,IIA
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3, 4, 4X
Buy America(n) Qualified	Contact Manufacturer

Conductor



Number Of Wires	4
Number Of Poles	3

Current

Amperage Rating	30 A
-----------------	------

Dimensions

Weight	1 lb.
--------	-------

General

Receptacle Type	Delayed Action
Type	Pin & Sleeve
Series	KP Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936370064

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)