



# KP Series 30 Amp Plug - D Type - 3P 4W Circuit - Grommet Range 0.375-0.625 Inch - 115/230VAC At 60Hz- Rotate Right

By Killark  
Catalog # [KP-304D23SU37](#)

KP Series - Aluminum 30 Amp Plug - D Type - 3W 4P Circuit - Grommet Range 0.375-0.625 Inch - 115/230VAC At 60Hz- Rotate Right

## Features

- Suitable where a connection is required for portable or movable equipment such as tools, motors, hand lights, etc.
- Solder Terminations for sure connection
- Copper free aluminum housing
- Delayed action contacts ensure safe interconnect
- Wide range of grommet openings
- Extra long grounding pin makes contact first and breaks contact last

## Specifications

|                          |                                                                                                                                                |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s)      | <ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB,IIA</li></ul> |
| EU RoHS Indicator        | Contact Manufacturer                                                                                                                           |
| Nema Rating              | 3, 4, 4X                                                                                                                                       |
| Buy America(n) Qualified | Contact Manufacturer                                                                                                                           |



## Conductor

|                 |   |
|-----------------|---|
| Number Of Wires | 4 |
| Number Of Poles | 3 |

## Current

|                 |      |
|-----------------|------|
| Amperage Rating | 30 A |
|-----------------|------|

## General

|                 |                                              |
|-----------------|----------------------------------------------|
| Receptacle Type | Delayed Action                               |
| Type            | Pin & Sleeve                                 |
| Series          | KP Series                                    |
| Material        | Aluminum, Copper Free (less than 4/10 of 1%) |
| UPC             | 783936042886                                 |

## Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)