



KP Series 60 Amp Plug - E Type - 3P 4W Circuit - Grommet Range 0.875-1.125 Inch - 115/230VAC 60Hz

By Killark
Catalog # [KP-604E45](#)

KP Series - Aluminum 60 Amp Plug - E Type - 3W 4P Circuit - Grommet Range 0.875-1.125 Inch - 115/230VAC 60Hz

Features

- Suitable where a connection is required for portable or movable equipment such as tools, motors, hand lights, etc.
- Solder Terminations for sure connection
- Copper free aluminum housing
- Delayed action contacts ensure safe interconnect
- Wide range of grommet openings
- Extra long grounding pin makes contact first and breaks contact last

Application

KP Series plugs are suitable: in hazardous locations due to the presence of flammable vapors or gases;where a heavy duty plug and receptacle is necessary;where a connection is required for portable or movable equipment such as tools, motors, hand lights

Specifications

EU RoHS Indicator	Contact Manufacturer
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB,IIA
Nema Rating	3, 4, 4X, 7(B, C, D), 9(F, G)
Buy America(n) Qualified	Contact Manufacturer
Conductor	
Number Of Wires	4
Wire Size	#8 AWG to #2 AWG



Number Of Poles	3
Current	
Amperage Rating	60 A
Dimensions	
Length	11.75 in
Gross Weight with Packaging	2.63
Width	4.75 in
Weight	2.63 lb.
Height	4 in
Dimensions	11.75 in x 4.75 in x 4 in

General

Series	KP Series
Color	Gray
Receptacle Type	Delayed Action
Type	Pin & Sleeve
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936370149

Operational

Operating Cycles	10,000 operations
------------------	-------------------

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)