



KP Series 60 Amp Plug - F Type - 3P 4W Circuit - Grommet Range 1.250-1.500 Inch - 115/230VAC 60Hz

By Killark
Catalog # [KP-604F34](#)

KP Series - Aluminum 60 Amp Plug - F Type - 3W 4P Circuit - Grommet Range 1.250-1.500 Inch - 115/230VAC 60Hz

Features

- Suitable where a connection is required for portable or movable equipment such as tools, motors, hand lights, etc.
- Solder Terminations for sure connection
- Copper free aluminum housing
- Delayed action contacts ensure safe interconnect
- Wide range of grommet openings
- Extra long grounding pin makes contact first and breaks contact last

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB,IIA
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3, 4, 4X, 7(B, C, D), 9(F, G)
Buy America(n) Qualified	Contact Manufacturer

Conductor



Number Of Wires	4
Number Of Poles	3

Current

Amperage Rating	60 A
-----------------	------

General

Receptacle Type	Delayed Action
Type	Pin & Sleeve
Series	KP Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936370163

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)