



# KR Series - 30 Amp Receptacle With Feed-Thru Enclosure - 3P 4W Circuit - 115/230VAC At 60Hz - Hub Size 1/2 Inch

By Killark  
Catalog # [KRS-218-1304](#)

KR Series - Aluminum 30 Amp Receptacle With Feed-Thru Enclosure - 3W 4P Circuit - 115/230VAC At 60Hz - Hub Size 1/2 Inch



## Features

- Suitable where a connection is required for portable or movable equipment such as tools, motors, hand lights, etc.
- Wire leads for termination
- Factory sealed receptacles
- Copper free aluminum housing
- Straight or angle type back boxes
- Delayed action contacts ensure safe interconnect
- Extra long grounding pin makes contact first and breaks contact last

## Specifications

Hazardous Rating(s)	<ul style="list-style-type: none"> <li>• Class I, Divisions 1 &amp; 2, Groups C, D</li> <li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li> </ul>
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3, 4, 4X, 7(B, C, D), 9(F, G)
Buy America(n) Qualified	Contact Manufacturer

## Conductor

Number Of Wires	4
Number Of Poles	3

## Configuration

Hub Pattern	Feed-Thru
-------------	-----------

## Current

Amperage Rating	30 A
-----------------	------

## Dimensions

Hub Size	1/2"
----------	------

## General

Receptacle Type	Delayed Action
Type	Pin & Sleeve
Series	KR Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936391922

## Logistics

Factory Sealed	Factory Sealed
Carton Quantity	1

## Product Assets

[Catalog \[English\]](#)