



KWPH100 - 100 Watt Quad Volt Metal Halide Wallpack Fixture

By Killark

Catalog # **KWPH100**

100 Watt Quad Volt Metal Halide Wallpack Fixture



Features

- Aluminum with Bronze finish 1/2" hub on either side for conduit entry.
- Mogul Porcelain Socket.
- Reflector is specular aluminum precision formed for optimal performance.
- Suitability for 55°C ambient, 90°C supply wire required.
- Lens thermal shock and impact resistant prismatic borosilicate glass.
- Full front access available for lamp or ballast service by hinging front door.
- Two Hubbell Guard® Corrosion resistant hex head fasteners provide water-tight seal for door gasket.
- Optional factory installed photocells, fusing, instant restrike, ballast protector, & lamps available.

Specifications

Nema Rating 4X

Hazardous Rating(s)

- Class I, Division 2, Groups A, B, C, D
- Class I, Zone 2, Groups IIC, IIB, IIA

EU RoHS Indicator

Contact Manufacturer

Current

Frequency Rating

60 Hz

Voltage Rating

120-277 VAC

Wattage

100 W

Dimensions

Weight

22.28 lb.

Hub Size

1/2"

General

UPC

783936377209

Light Source

Metal Halide

Series

KWP Series



A Hubbell brand