



KWPH106 - 100 Watt 347 Volt Metal Halide Wallpack Fixture

By Killark
Catalog # KWPH106

100 Watt 347 Volt Metal Halide Wallpack Fixture

Features

- Aluminum with Bronze finish 1/2" hub on either side for conduit entry.
- Mogul Porcelain Socket.
- Reflector is specular aluminum precision formed for optimal performance.
- Suitability for 55°C ambient, 90°C supply wire required.
- Lens thermal shock and impact resistant prismatic borosilicate glass.
- Full front access available for lamp or ballast service by hinging front door.
- Two Hubbell Guard® Corrosion resistant hex head fasteners provide water-tight seal for door gasket.
- Optional factory installed photocells, fusing, instant restrike, ballast protector, & lamps available.

Specifications

Nema Rating	4X
Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D



EU RoHS Indicator

- Class I, Zone 2, Groups IIC, IIB, IIA
- Contact Manufacturer

Current

Frequency Rating	60 Hz
Voltage Rating	120-347 VAC
Wattage	100 W

Dimensions

Weight	22.28 lb.
Hub Size	1/2"

General

UPC	783936377254
Light Source	Metal Halide
Series	KWP Series

Logistics

Carton Quantity	1
-----------------	---