



KWPL433 - 4,000 Lumen Range 347-480 Volt LED Wallpack Fixture

By Killark
Catalog # [KWPL433](#)

4,000 Lumen Range 347-480 Volt LED Wallpack Fixture

Features

- Aluminum with Bronze finish 1/2" hub on either side for conduit entry.
- Suitability for 55°C ambient, 90°C supply wire required.
- Lens thermal shock and impact resistant prismatic borosilicate glass.
- Two Hubbell Guard® Corrosion resistant hex head fasteners provide water-tight seal for door gasket.
- Optional factory installed photocells & fusing available.

Specifications

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA
EU RoHS Indicator	Contact Manufacturer
Nema Rating	4X
Buy America(n) Qualified	Contact Manufacturer



Current

Voltage Rating	347-480 VAC
----------------	-------------

Dimensions

Hub Size	1/2"
Weight	14 lb.

General

Series	KWPL Series
UPC	783936143613
Light Source	LED

Operational

Lumens	4436
Lumen Range	2,001-5,000 lm

Product Assets

[Catalog \[English\]](#)



A Hubbell brand