



L1L1030C - L1L Series 10,000 Lumen Output 5000K CCT, 120-277 Universal Voltage With Clear Glass Optic

By Killark
Catalog # [L1L1030C](#)

L1L Series 10,000 Lumen Output 5000K CCT, 120-277 Universal
Voltage With Clear Glass Optic

Features

- Tool-less access to wiring chamber
- Slot-back design allows for a 5/16 or M8 bolt to be mounted anywhere along the back of the luminaire
- High Efficacy up to 153 lumens per watt delivered
- Corrosion resistant Copper-free housing
- Standard supplemental 6KV surge protection
- Optional supplementary surge protection available 20KA/10KV (120-277 VAC), 10KA/10KV (347-480 VAC)

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
IP Rating	IP66
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Current

Lumens Per Watt	148.8
Wattage	68.5 W
Voltage Rating	120-277 VAC



Dimensions

Hub Size	3/4"
----------	------

General

Type	Linear Light Fixture
Series	L1L Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Natural
Optic Type	Glass Lens
UPC	783936174532
Light Source	LED
Mounting Type	Pendant or Surface

Operational

Color Temperature	5000 K
Lumens	10190
Lumen Range	10,001-15,000 lm

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)