



LL78 - 2-1/2" LL Hub, Iron Duraloy 8 Conduit Body

By Killark
Catalog # [LL78](#)

2-1/2" LL Hub, Iron Duraloy 8 Conduit Body



Features

- Completely interchangeable with competitive bodies, gaskets, and covers.
- Flat back design provides greater cubic capacity for easier wire pulling and more room for splicing.
- Raintight when used with gasketed covers.
- Stainless steel screws on stamped and cast covers.
- Smooth integral wire bushings.

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

Specifications

Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
EU RoHS Indicator	Contact Manufacturer

UL File Number	E3397
CSA File Number	LR11852
Buy America(n) Qualified	Contact Manufacturer

Configuration

Hub Pattern	LL
-------------	----

Dimensions

Gross Weight with Packaging	14.6
Hub Size	2-1/2"

General

Type	Conduit Body
Series	Duraloy 8 Series
Material	Iron
Finish Type	Powder Epoxy Paint
UPC	783936481210
Color	Gray

Product Assets

[Catalog \[English\]](#)