



LZ2N32230-55C

By Killark
Catalog # LZ2N32230-55C

LZ2N Series - Non-Metallic 32 Watt Fluorescent Light Fixture
(Two 4-Footlamps Not Included) - Double-Ended Lamp Type -
120-277V At 50/60Hz - Hubsizes 3/4 -55C Ambient Suitable.



Features

- Lexan® Clear Lens, impact resistant polycarbonate
- Housing-one piece fiberglass reinforced polyester, NEMA 4X & IP66 rated.
- Two 3/4" NTP aluminum hubs - one at each end (includes one 3/4" close-up plug and two 3/4" x 1/2" reducers for maximum user flexibility)
- Two 1/4"-20 aluminum bushings furnished in top of fixture for threaded rod
- 2' and 4' luminaries
- Lamp types Linear 17, 28, 32, 40, 44, 54, 60W Long compact 40, 55W (single ended)
- Electronic ballast standard
- World voltage (most models) 120 thru 277V, 50/60 Hz

General

Finish Type	Naturel
Lamp Type	T8
Light Source	Linear Fluorescent
Material	Polyester, Fiberglass Reinforced
Mounting Type	• Pendant • Surface
Optic Type	Polycarbonate Lens - Clear
Series	LZ2N
UPC	783936094021

Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	120-277 VAC
Wattage	32 W

Certifications and Compliance

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
IP Rating	IP66

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - KIL_LZ2N Series Fluorescent Luminaires IOM_K1267](#)
[Photometry - KIL_LZ2x322](#)



A proud member of the Hubbell Family.