



MBH700NR - MB Series, AL 70 Watt Medium Base Metal Halide HID Light Fixture (Lamp Not Included), Quadri-Volt (120/208/240/277V), 60Hz, Ex nR

By Killark
Catalog # [MBH700NR](#)

MB Series - Aluminum 70 Watt Medium Base Metal Halide HID Light Fixture (Lamp Not Included) - Quadri-Volt (120/208/240/277V) At 60Hz - Ex nR

Features

- Ballast tank and splice box – corrosion resistant copper-free aluminum alloy
- Baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection
- All external hardware – stainless steel
- Guard – copper-free aluminum alloy
- Normally shipped as components for quick delivery
- Refractor guard – steel with corrosion resistant finish
- Reflector – lightweight, corrosion resistant fiberglass reinforced polyester
- Fluorescent models furnished with lamps.
- Energy efficient instant on white light (2700K). 10,000 hour lamp life
- HID lamp holders are E26 medium base

Specifications

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G
---------------------	--



EU RoHS Indicator	• Class III, Divisions 1 & 2
Buy America(n) Qualified	Contact Manufacturer
	Contact Manufacturer
Current	
Frequency Rating	60 Hz
Wattage	70 W
Voltage Rating	Quad - 120/277/347/480 VAC
General	
Series	MB Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Lamp Type	Medium Base
Optic Type	Luminaire Only
UPC	783936995533
Light Source	Metal Halide
Mounting Type	Luminaire Only

Product Assets

[Catalog \[English\]](#)