



# MBI20-GGD4R-SU104

By Killark  
Catalog # [MBI20-GGD4R-SU104](#)

MB N4X Stanchion Assembly - Red.



### Features

- Ballast tank and splice box – corrosion resistant copper-free aluminum alloy
- Baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection
- All external hardware – stainless steel
- Guard – copper-free aluminum alloy
- Normally shipped as components for quick delivery
- Refractor guard – steel with corrosion resistant finish
- Reflector – lightweight, corrosion resistant fiberglass reinforced polyester
- Fluorescent models furnished with lamps.
- Energy efficient instant on white light (2700K). 10,000 hour lamp life
- HID lamp holders are E26 medium base

### General

|               |                                              |
|---------------|----------------------------------------------|
| Finish Type   | Peinture époxy en poudre                     |
| Light Source  | Incandescent - Medium Base                   |
| Material      | Aluminum, Copper Free (less than 4/10 of 1%) |
| Mounting Type | Stanchion 25°                                |
| Optic Type    | Glass Globe - Fluted                         |
| Series        | MB                                           |
| UPC           | 783936044200                                 |

### Dimensions

|          |        |
|----------|--------|
| Hub Size | 1-1/4" |
|----------|--------|

### Certifications and Compliance

|                     |                                                                                                                                                                                                                                           |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Division 2, Groups A, B, C, D</li><li>• Class I, Zone 2, Groups IIC, IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul> |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### Product Assets

[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.