



# MBL101-GGX2 NR - 100W HPS Fluorescent 120V 3/4" Ceiling Mount with Globe and Guard- Ex nR

By Killark  
Catalog # [MBL101-GGX2 NR](#)

100W HPS Fluorescent 120V 3/4" Ceiling Mount with Globe and  
Guard- Ex nR

## Features

- Ballast tank and splice box – corrosion resistant copper-free aluminum alloy
- Baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection
- All external hardware – stainless steel
- Guard – copper-free aluminum alloy
- Normally shipped as components for quick delivery
- Refractor guard – steel with corrosion resistant finish
- Reflector – lightweight, corrosion resistant fiberglass reinforced polyester
- Fluorescent models furnished with lamps.
- Energy efficient instant on white light (2700K). 10,000 hour lamp life
- HID lamp holders are E26 medium base

## Specifications

|                     |                                                                                                                                                                                                                                           |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Division 2, Groups A, B, C, D</li><li>• Class I, Zone 2, Groups IIC, IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul> |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|



|                                   |                                              |
|-----------------------------------|----------------------------------------------|
| EU RoHS Indicator                 | Contact Manufacturer                         |
| Buy America(n) Qualified          | Contact Manufacturer                         |
| <b>Current</b>                    |                                              |
| Frequency Rating                  | 60 Hz                                        |
| Wattage                           | 100 W                                        |
| Voltage Rating                    | 120 VAC                                      |
| <b>Dimensions</b>                 |                                              |
| Hub Size                          | 3/4"                                         |
| <b>General</b>                    |                                              |
| Series                            | MB Series                                    |
| Material                          | Aluminum, Copper Free (less than 4/10 of 1%) |
| Finish Type                       | Powder Epoxy Paint                           |
| Lamp Type                         | Medium Base                                  |
| Optic Type                        | Glass Globe - Fluted                         |
| UPC                               | 783936044378                                 |
| Light Source                      | High Pressure Sodium                         |
| Mounting Type                     | Ceiling                                      |
| <b>Product Assets</b>             |                                              |
| <a href="#">Catalog [English]</a> |                                              |