



MBL151NREB - MB Series - Aluminum 150 Watt Medium Base High Pressure Sodium HID Light Fixture with Eyebolts (Lamp Not Included) - 120V At 60Hz - Ex nR

By Killark
Catalog # [MBL151NREB](#)

MB Series - Aluminum 150 Watt Medium Base High Pressure Sodium HID Light Fixture with Eyebolts (Lamp Not Included) - 120V At 60Hz - Ex nR

Features

- Ballast tank and splice box – corrosion resistant copper-free aluminum alloy
- Baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection
- All external hardware – stainless steel
- Guard – copper-free aluminum alloy
- Normally shipped as components for quick delivery
- Refractor guard – steel with corrosion resistant finish
- Reflector – lightweight, corrosion resistant fiberglass reinforced polyester
- Fluorescent models furnished with lamps.
- Energy efficient instant on white light (2700K). 10,000 hour lamp life
- HID lamp holders are E26 medium base

Specifications

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G
---------------------	--



EU RoHS Indicator
Buy America(n) Qualified

- Class III, Divisions 1 & 2
- Contact Manufacturer
Contact Manufacturer

Current

Frequency Rating	60 Hz
Wattage	150 W
Voltage Rating	120 VAC

General

Series	MB Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Lamp Type	Medium Base
Optic Type	Luminaire Only
UPC	783936044545
Light Source	High Pressure Sodium
Mounting Type	Luminaire Only

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)