



# MBL501-GB2 - 50W HPS Fluorescent 120V 3/4" Wall Mount

By Killark  
Catalog # [MBL501-GB2](#)

50W HPS Fluorescent 120V 3/4" Wall Mount

## Features

- Ballast tank and splice box – corrosion resistant copper-free aluminum alloy
- Baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection
- All external hardware – stainless steel
- Guard – copper-free aluminum alloy
- Normally shipped as components for quick delivery
- Refractor guard – steel with corrosion resistant finish
- Reflector – lightweight, corrosion resistant fiberglass reinforced polyester
- Fluorescent models furnished with lamps.
- Energy efficient instant on white light (2700K). 10,000 hour lamp life
- HID lamp holders are E26 medium base

## Specifications

|                          |                                                                                                                                                                                                                                           |
|--------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s)      | <ul style="list-style-type: none"><li>• Class I, Division 2, Groups A, B, C, D</li><li>• Class I, Zone 2, Groups IIC, IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul> |
| EU RoHS Indicator        | Contact Manufacturer                                                                                                                                                                                                                      |
| Buy America(n) Qualified | Contact Manufacturer                                                                                                                                                                                                                      |



## Current

|                  |         |
|------------------|---------|
| Frequency Rating | 60 Hz   |
| Wattage          | 50 W    |
| Voltage Rating   | 120 VAC |

## Dimensions

|          |      |
|----------|------|
| Hub Size | 3/4" |
|----------|------|

## General

|               |                                              |
|---------------|----------------------------------------------|
| Series        | MB Series                                    |
| Material      | Aluminum, Copper Free (less than 4/10 of 1%) |
| Finish Type   | Powder Epoxy Paint                           |
| Lamp Type     | Medium Base                                  |
| Optic Type    | Glass Globe - Fluted                         |
| UPC           | 783936994727                                 |
| Light Source  | High Pressure Sodium                         |
| Mounting Type | Wall Bracket                                 |

## Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

## Product Assets

[Catalog \[English\]](#)