



MBL701-GB3 - 70W HPS Fluorescent 120V 1" Wall Mount

By Killark
Catalog # [MBL701-GB3](#)

70W HPS Fluorescent 120V 1" Wall Mount

Features

- Ballast tank and splice box – corrosion resistant copper-free aluminum alloy
- Baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection
- All external hardware – stainless steel
- Guard – copper-free aluminum alloy
- Normally shipped as components for quick delivery
- Refractor guard – steel with corrosion resistant finish
- Reflector – lightweight, corrosion resistant fiberglass reinforced polyester
- Fluorescent models furnished with lamps.
- Energy efficient instant on white light (2700K). 10,000 hour lamp life
- HID lamp holders are E26 medium base

Specifications

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer



Current

Frequency Rating	60 Hz
Wattage	70 W
Voltage Rating	120 VAC

Dimensions

Hub Size	1"
----------	----

General

Series	MB Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Lamp Type	Medium Base
Optic Type	Glass Globe - Fluted
UPC	783936995106
Light Source	High Pressure Sodium
Mounting Type	Wall Bracket

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Catalog \[English\]](#)