



Wall Mount
Incandescent




Wall Mount
Fluorescent



Wall Mount with
Extension and Dome
Reflector accessories

Class I, Div. 2, Groups A,B,C,D
Class I, Zone 2, Groups IIC,IIB,IIA
Class II, Div. 2, Groups F,G
Class III
Marine
NEMA 3, 4, 4X, IP66



ABS Type Approval

COMPONENT PARTS



Pendant



Ceiling/Wall



Wall Elbow



Ceiling/Wall
(Interior Detail)



Incandescent



Fluorescent



Globe



Guard



Reflector



Extension



Gray Blank



Clear

NV2 SPLICE BOXES - INCLUDES SILICONE GASKETS & BRASS SCREWS

CATALOG NUMBER	DESCRIPTION		
NV2AG	Pendant	3/4" NPT	Pendant splice box includes a 316 stainless steel set screw at the conduit connection
NV2XG ^①	Ceiling Box	3/4" NPT	Ceiling box vol. 24 cu. inches
NV2MG ^①		M20	
NV2BG	Wall Bracket		Use with NV2XG or NV2MG for wall mount

NV2 BODIES

CATALOG NUMBER	DESCRIPTION
NV2IG15	Incandescent Body with E-26 medium base socket; fixture rated voltage 277VAC max.
NV2FG13	13 W Fluorescent Body World Voltage 120V - 277V 50/60Hz
NV2FG18	18 W Fluorescent Body World Voltage 120V - 277V 50/60Hz
NV2FG26	26 W Fluorescent Body World Voltage 120V - 277V 50/60Hz
NV2FG32	32 W Fluorescent Body World Voltage 120V - 277V 50/60Hz
NV2FG42	42 W Fluorescent Body World Voltage 120V - 277V 50/60Hz

NV2 GLASS GLOBES & GUARDS^②

CATALOG NUMBER	DESCRIPTION	
VCG-100	Clear	150 watt Lamp size A-21 max.
VCGP-100	Clear, Tempered	
NV2GG	Guard	

NV2 REFLECTORS AND EXTENSION

CATALOG NUMBER	DESCRIPTION
NVPSD12	White Polycarbonate Reflector (secured by guard)
NVEXTG	Extension (for wall mount fixture with reflector)

BLANK COVERS FOR NV2XG CEILING BOXES

CATALOG NUMBER	DESCRIPTION
NV2CG	Gray Cover
NV2CC ^①	Clear Cover

NV2F FLUORESCENT REPLACEMENT LAMPS AND BALLASTS

CATALOG NUMBER	LAMP	BALLAST
MQL13	13 W Quad-Pin Lamp 900 Lumens	BKF131830 13/18 Watt Rep. Ballast
MQL18	18 W Quad-Pin Lamp 1200 Lumens	
MQL26	26 W Quad-Pin Lamp 1800 Lumens	
MQL32	32 W Quad-Pin Lamp 2400 Lumens	BKF26324230 26/32/42 Watt Rep. Ballast
MQL42	42 W Quad-Pin Lamp 3200 Lumens	

^① NV2 ceiling (wall) boxes have 4 10-32 brass inserts with 2 ground screws. May be used for wet locations, as terminal/junction, boxes, or instruments using 'clear' blank cover.

^② See page L12 for colored globes; use tempered for wet locations.

