



NV2FG32ASG - 32W 120-277V Fluorescent Pendant with Standard Globe and Guard

By Killark
Catalog # [NV2FG32ASG](#)

32W 120-277V Fluorescent Pendant with Standard Globe and Guard

Features

- NV2 Series non-metallic light fixtures combine an outstanding balance of strength, stiffness, toughness and electrical properties
- Energy and labor saving fluorescent or incandescent models
- Accessories include polycarbonate dome reflectors and wall extension
- Molded from 30% glass-filled thermoset polyester for high strength
- Resists corrosive effects of most chemicals, hydrocarbons and solvents
- Designed for indoor and outdoor, globe down applications.

Specifications

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Division 2, Groups F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer



Current

Frequency Rating	50/60 Hz
Wattage	32 W
Voltage Rating	120-277 VAC

Dimensions

Hub Size	3/4"
----------	------

General

Series	NV Series
Material	Polyester, Fiberglass Reinforced
Finish Type	Powder Epoxy Paint
Lamp Type	Bi Pin
Optic Type	Glass Globe - Clear
UPC	783936050805
Light Source	Compact Fluorescent
Mounting Type	Pendant

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)