



OE-1 - 1/2" E Hub, Aluminum O Series Conduit Body

By Killark
Catalog # [OE-1](#)

1/2" E Hub, Aluminum O Series Conduit Body



Features

- Raintight when used with gasketed covers.
- Malleable iron suitable for use in concrete.
- Interchangeable with competitive products.
- Stainless steel screws on stamped and cast covers.
- Tapered threaded hubs (NPT).

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

Specifications

EU RoHS Indicator	Contact Manufacturer
CSA File Number	LR11852
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E3397
Buy America(n) Qualified	Contact Manufacturer

Configuration

Hub Pattern	E
Dimensions	
Hub Size	1/2"
Length	5 in
Gross Weight with Packaging	0.28
Width	2 in
Weight	0.28 lb.
Height	2 in
Dimensions	5 in x 2 in x 2 in
General	
Series	O Series
Color	Gray
Type	Conduit Body
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936471013
Logistics	
Carton Quantity	10
Product Assets	
Catalog [English]	