



OX-6 - 2" X Hub, Aluminum O Series Conduit Body

By Killark
Catalog # OX-6

2" X Hub, Aluminum O Series Conduit Body



Features

- Raintight when used with gasketed covers.
- Malleable iron suitable for use in concrete.
- Interchangeable with competitive products.
- Stainless steel screws on stamped and cast covers.
- Tapered threaded hubs (NPT).

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

Specifications

Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
EU RoHS Indicator	Contact Manufacturer
UL File Number	E3397
CSA File Number	LR11852

Configuration

Hub Pattern	X
-------------	---

Dimensions

Gross Weight with Packaging	2.5
Hub Size	2"
Width	6 in
Height	4 in
Length	12 in
Dimensions	12 in x 6 in x 4 in

General

Type	Conduit Body
Series	O Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936550060
Color	Gray

Logistics

Carton Quantity	2
-----------------	---

Product Assets

[Catalog \[English\]](#)