



TB58 - 1-1/2" TB Hub, Iron Duraloy 8 Conduit Body,

By Killark
Catalog # [TB58](#)

1-1/2" TB Hub, Iron Duraloy 8 Conduit Body,



Features

- Completely interchangeable with competitive bodies, gaskets, and covers.
- Flat back design provides greater cubic capacity for easier wire pulling and more room for splicing.
- Raintight when used with gasketed covers.
- Stainless steel screws on stamped and cast covers.
- Smooth integral wire bushings.

Application

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

Specifications

Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
EU RoHS Indicator	Contact Manufacturer
UL File Number	E3397
CSA File Number	LR11852

Buy America(n) Qualified

Contact Manufacturer

Configuration

Hub Pattern	TB
-------------	----

Dimensions

Gross Weight with Packaging	5.4
Hub Size	1-1/2"
Width	6.25 in
Height	3.375 in
Length	13.25 in
Dimensions	13.25 in x 6.25 in x 3.375 in

General

Type	Conduit Body
Series	Duraloy 8 Series
Material	Iron
Finish Type	Powder Epoxy Paint
UPC	783936481432
Color	Gray

Product Assets

[Catalog \[English\]](#)