



UGFI20AD-GRN

By Killark
Catalog # [UGFI20AD-GRN](#)

20A, 125VAC Portable GFCI Receptacle With Green LED

Features

- No need to permanently alter existing installations
- Portable Unit can be temporarily hung using included strap near an existing receptacle wherever protection is required.
- Factory Sealed Unit.
- Acceptor® plug and cord set included with Adapter Unit. Cord is 36".
- GFCI device also provides circuit protection, for connected apparatus, against current overload and short circuits.
- Acceptor® receptacles and plugs are intermateable with both Crouse-Hinds® ArkGard®2 and Appleton® U-Line® products.
- Amber pilot light provides indication that the receptacle is energized.
- Units can be Padlocked OFF for maintained safety.
- Fully gasketed GFCI compartment prevents moisture from damaging electronic components.
- Same high quality materials as the standard ACCEPTOR®.

Specifications

UL File Number	E91049
CSA File Number	LR14667



Hazardous Rating(s)	• Class 1, Division 2, Groups B, C, D • Class I, Zone 2, Groups IIB+H2, IIA • Class II, Divisions 1 & 2, Groups F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer

Current

Amperage Rating	20
Voltage Rating	125 VAC

Dimensions

Weight	16 lb.
--------	--------

General

UPC	783936660899
Series	UGFI Series

Product Assets

[Installation Manual \[English\]](#)