



UGRA



XHL



XHLF



UGRGF

FEATURES-SPECIFICATIONS

UNIVERSAL ADAPTER KIT

ACCEPTOR® receptacles are available with an adapter kit for mounting to Crouse-Hinds® EDS Series or Appleton® EFD Series back boxes.

ACCEPTOR receptacles properly installed with these adapter kits are U.L. Listed for use in Class I, Div. 2, Groups B,C,D hazardous locations and Zone II, Groups IIB + H2, IIA.

Kit contains one ACCEPTOR® receptacle plus adapter plate and mounting bolts.

UGRA ADAPTER KIT	
NEMA RATING & CONFIGURATION	ADAPTER KIT CATALOG NUMBER
20 Amp 125 Volt 2 POLE 3 WIRE 5-20R	UGRA-20231
20 Amp 250 Volt 2 POLE 3 WIRE 6-20R	UGRA-20232

UL Listed File No. E91049

SP Certified LR14667

XHL SERIES HAND LAMPS

A handy accessory to the ACCEPTOR® Series, these hand lamps can be used as an illumination source where flammable materials are present, such as processed finish goods, storage vats, or handling areas.

See page L14 for detailed information and features.

XHL INCANDESCENT	
CATALOG NUMBER	DESCRIPTION
XHL-100	Handlamp
XHL-GL	Replacement globe
XHLG	Replacement guard
XHLS	Replacement socket

XHL Incandescent
Class I, Div. 1 & 2, Groups C,D
Class I, Zones 1 & 2, Groups IIB,IIA

UL Listed File No. E97760

SP Certified File No. LR10019

XHLF FLUORESCENT (120VAC)

CATALOG NUMBER	DESCRIPTION
XHLF26	Fluorescent hand lamp
XHLF26-50KP	Fluorescent hand lamp with 50' of 16/3 SOW cord and 15A Acceptor plug

XHLF Fluorescent
Class I, Div. 1 & 2, Groups C,D
Class I, Zones 1 & 2, Groups IIB,IIA
Class II, Div. 1 & 2, Groups E,F,G

UL cUL Listed File No. E97760

GFI PROTECTED RECEPTACLE

Utilizes FXS GFI and ACCEPTOR® receptacle to interrupt a circuit, when a ground fault is detected on equipment which may be handled by personnel in hazardous locations.

Features

- Factory Sealed
- Test and Reset push buttons are provided on cover assembly, with optional pilot light available. Unit should be tested monthly
- Includes new GFCI to meet latest UL943 GFCI standards revisions
- Exterior gasket provides NEMA 3 weatherproof protection
- Ground boss for grounding in the splice box
- Color coded wiring and stainless steel cover bolts
- Receptacle used is UGRO-20231. See page PR23

NEMA RATING & CONFIGURATION	ENCLOSURE STYLE	HUB SIZE	CATALOG® NUMBER
20A, 125V, 2P, 3W	Dead End	1/2"	UGRGF107
	Dead End	3/4"	UGRGF108
	Dead End	1"	UGRGF109
	Feed Thru	1/2"	UGRGF110
	Feed Thru	3/4"	UGRGF111
	Feed Thru	1"	UGRGF112

Electrical Rating

GFI units are rated at 20A, 120 VAC, 60Hz. Class A.

4-6 milliamp trip setting

Trip Time-UL Curve

Class I, Div. 1 & 2, Groups C,D
Class I, Zones 1 & 2, Groups IIB,IIA
Class II, Div. 1 & 2, Groups F,G
Class III
NEMA 3, 7(C,D) 9(F,G)

SP Certified LR11714

See files for details or call Killark.

For Red LED pilot light indicator of live circuit, add "-PL" to catalog number.

Example - UGRGF107-PL.