



# UGR Series 20A 125V, Group B Acceptor, 1" Dead End, Quick-Wire

By Killark  
Catalog # [UGRB3-20231QW](#)

20A 125V, Group B Acceptor, 1" Dead End, Quick-Wire

## Features

- Factory sealed chamber in UGR receptacle contains switch's arcing components.
- Spring loaded receptacle cover closes when plug is removed.
- Copper-free aluminum (less than 4/10 of 1%) alloy resists corrosion
- Electrostatically applied and baked powder epoxy/polyester finish
- ACCEPTOR® plugs conform to NEMA configurations, while it's "turn to engage" feature locks in plug and can be used to prevent accidental disengagement of critical equipment.
- Plugs for use with type S/SO/ST/STO heavy duty cord.

## Specifications

|                          |                                                                                                                                                                                                                                                     |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s)      | <ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups B, C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB+H2, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul> |
| EU RoHS Indicator        | Contact Manufacturer                                                                                                                                                                                                                                |
| Nema Rating              | 3, 4, 4X, 7(B, C, D), 9(F, G)                                                                                                                                                                                                                       |
| Buy America(n) Qualified | Contact Manufacturer                                                                                                                                                                                                                                |

## Conductor



|                 |   |
|-----------------|---|
| Number Of Wires | 3 |
| Number Of Poles | 2 |

## Configuration

|             |          |
|-------------|----------|
| Hub Pattern | Dead-End |
|-------------|----------|

## Current

|                 |      |
|-----------------|------|
| Amperage Rating | 20 A |
|-----------------|------|

## Dimensions

|          |    |
|----------|----|
| Hub Size | 1" |
|----------|----|

## General

|                 |                                              |
|-----------------|----------------------------------------------|
| Receptacle Type | Delayed Action                               |
| Type            | Straight Blade                               |
| Series          | UGR Series                                   |
| Material        | Aluminum, Copper Free (less than 4/10 of 1%) |
| UPC             | 783936124612                                 |

## Logistics

|                |                |
|----------------|----------------|
| Factory Sealed | Factory Sealed |
|----------------|----------------|

## Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)