



UGR Series 15A 125V, Group B Acceptor, 1" Feed-Thru, Quick-Wire

By Killark
Catalog # [UGRB6C-15231QW](#)

15A 125V, Group B Acceptor, 1" Feed-Thru, Quick-Wire

Features

- Factory sealed chamber in UGR receptacle contains switch's arcing components.
- Spring loaded receptacle cover closes when plug is removed.
- Copper-free aluminum (less than 4/10 of 1%) alloy resists corrosion
- Electrostatically applied and baked powder epoxy/polyester finish
- ACCEPTOR® plugs conform to NEMA configurations, while it's "turn to engage" feature locks in plug and can be used to prevent accidental disengagement of critical equipment.
- Plugs for use with type S/SO/ST/STO heavy duty cord.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB+H2, IIA • Class II, Divisions 1 & 2, Groups F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3, 4, 4X, 7(B, C, D), 9(F, G)
Buy America(n) Qualified	Contact Manufacturer

Conductor



Number Of Wires	3
Number Of Poles	2

Configuration

Hub Pattern	Feed-Thru
-------------	-----------

Current

Amperage Rating	15 A
-----------------	------

Dimensions

Hub Size	1"
----------	----

General

Receptacle Type	Delayed Action
Type	Straight Blade
Series	UGR Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936125411

Logistics

Factory Sealed	Factory Sealed
----------------	----------------

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)