



UGRC-20232FQW

By Killark
Catalog # [UGRC-20232FQW](#)

20A 250V Acceptor Connectors with Flip Style Cap, Quick-Wire



Features

- In-line connector allows for extending reach of portable equipment.
- Available with Exclusive Breech-Lock Lid
- Patented lid notch allows for screwdriver, etc. to hold open lid for easier, two-hand installation.
- Factory Sealed Construction
- Copper-free aluminum (less than 4/10 of 1%) alloy resists corrosion
- Electrostatically applied and baked powder epoxy/polyester finish
- Dead Front Construction with Integral Switch - requires Hazardous Rated NEMA-Bladed Plug for operation

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D
	• Class I, Zones 1 & 2, Groups IIB+H2, IIA
	• Class II, Divisions 1 & 2, Groups F, G

EU RoHS Indicator

- Class III, Divisions 1 & 2
Contact Manufacturer

Conductor

Number Of Poles	2
Number Of Wires	3

Current

Amperage Rating	20 A
-----------------	------

General

UPC	783936124902
Type	Straight Blade
Receptacle Type	Delayed Action
Material	Aluminum, Copper Free (less than 4/10 of 1%)

Logistics

Factory Sealed	Factory Sealed
----------------	----------------